



Specifications Sigrow BV Mass Start Scale 2020
Wageningen, The Netherlands



| Name | Sigrow Mass Start Scale v1 / Scale |
|---|--|
| Standard dimensions | 330 x 560 mm (ϕ) |
| Height with tray | 45 mm |
| Maximum Weight | 20 Kg (ϕ) |
| Resolution | 1 gram |
| Accuracy | ±20 grams |
| Output format via api.sigrow.com | JSON file |
| Sampling time | 5'-15' <i>set at manufacturing</i> |
| Required components | Sigrow® Central station for each 150 devices |
| Lead time | 3 weeks from purchase date for up to 50 devices |
| Maximum radio range | 300 meters |
| Battery life | +4 months on 2xAA batteries |
| Enclosure rating | IP65 |





(c) **Customization service:** Scale dimensions, number of industrial load cells, sampling time, number of batteries can be customised on demand.



Easy to start: Place dry tray on top, hold zero button, place your wet tray on top. You are ready to see your data in app.sigrow.com or integrate with your server using api.sigrow.com



sense

discover

improve